

ELECTRON WORK FUNCTION OF THE ELEMENTS

The electron work function Φ is a measure of the minimum energy required to extract an electron from the surface of a solid. It is defined more precisely as the energy difference between the state in which an electron has been removed to a distance from the surface of a single crystal face that is large enough that the image force is negligible but small compared to the distance to any other face (typically about 10^{-4} cm) and the state in which the electron is in the bulk solid. In general, Φ differs for each face of a monocrystalline sample.

Since Φ is dependent on the cleanliness of the surface, measurements reported in the literature often cover a considerable range. This table contains selected values for the electron work function of the elements which may be regarded as typical values for a reasonably clean surface. The method of measurement is indicated for each value. The following abbreviations appear:

- TE — Thermionic emission
- PE — Photoelectric effect
- FE — Field emission
- CPD — Contact potential difference
- polycr — Polycrystalline sample
- amorph — Amorphous sample

Values in parentheses are only approximate.

REFERENCES

1. Hödl, J., and Schulte, F. K., Work Functions of Metals, in *Solid Surface Physics*, Höhler, G., Editor, Springer-Verlag, Berlin, 1979.
2. Riviere, J. C., Work Function: Measurements and Results, in *Solid State Surface Science, Vol. I*, Green, M., Editor, Decker, New York, 1969.
3. Michaelson, H. B., *J. Appl. Phys.*, 48, 4729, 1977.

Element	Plane	Φ/eV	Method	Element	Plane	Φ/eV	Method	Element	Plane	Φ/eV	Method	
Ag	100	4.64	PE	K	210	5.00	PE	Ru	polycr	4.71	PE	
	110	4.52	PE		polycr	2.29	PE	Sb	amorph	4.55		
	111	4.74	PE		La	polycr	3.5	PE	100	4.7		
Al	100	4.20	PE	Li	polycr	2.93	FE	Sc	polycr	3.5	PE	
	110	4.06	PE		Lu	polycr	(3.3)	CPD	Se	polycr	5.9	PE
	111	4.26	PE		Mg	polycr	3.66	PE	Si	n	4.85	CPD
As	polycr	(3.75)	PE	Mn	polycr	4.1	PE	p 100		(4.91)	CPD	
Au	100	5.47	PE		100	4.53	PE	p 111		4.60	PE	
	110	5.37	PE		110	4.95	PE	Sm	polycr	2.7	PE	
	111	5.31	PE		111	4.55	PE	Sn	polycr	4.42	CPD	
B	polycr	(4.45)	TH	Na	112	4.36	PE	Sr	polycr	(2.59)	TH	
Ba	polycr	2.52	TH		114	4.50	PE	Ta	polycr	4.25	TH	
Be	polycr	4.98	PE		332	4.55	PE	100	4.15	TH		
Bi	polycr	4.34	PE	Nb	polycr	2.36	PE	110		4.80	TH	
C	polycr	(5.0)	CPD		001	4.02	TH	111		4.00	TH	
Ca	polycr	2.87	PE		110	4.87	TH	Tb	polycr	3.0	PE	
Cd	polycr	4.08	CPD	Pb	111	4.36	TH	Te	polycr	4.95	PE	
Ce	polycr	2.9	PE		112	4.63	TH	Th	polycr	3.4	TH	
Co	polycr	5.0	PE		113	4.29	TH	Ti	polycr	4.33	PE	
Cr	polycr	4.5	PE	Cs	116	3.95	TH	Tl	polycr	(3.84)	CPD	
Cs	polycr	1.95	PE		310	4.18	TH	U	polycr	3.63	PE	
Cu	100	5.10	FE		polycr	3.2	PE	100		3.73	PE	
	110	4.48	PE	Nd	100	5.22	PE	110		3.90	PE	
	111	4.94	PE		110	5.04	PE	113		3.67	PE	
	112	4.53	PE		111	5.35	PE	V	polycr	4.3	PE	
Eu	polycr	2.5	PE	Os	polycr	5.93	PE	W	polycr	4.55	CPD	
Fe	100	4.67	PE		polycr	4.25	PE	100		4.63	FE	
	111	4.81	PE		polycr	5.22	PE	110		5.22	FE	
Ga	polycr	4.32	PE	Pt	111	5.6	PE	111		4.45	FE	
Gd	polycr	2.90	CPD		polycr	5.64	PE	113		4.46	FE	
Ge	polycr	5.0	CPD		110	5.84	FE	116		4.32	TH	
Hf	polycr	3.9	PE	Rb	111	5.93	FE	Y	polycr	3.1	PE	
Hg	liquid	4.475	PE		320	5.22	FE	Zn	polycr	3.63	PE	
In	polycr	4.09	PE		331	5.12	FE		polycr	(4.9)	CPD	
Ir	100	5.67	PE	Re	polycr	2.261	PE	Zr	polycr	4.05	PE	
	110	5.42	PE		polycr	4.72	TE					
	111	5.76	PE		polycr	4.98	PE					